

membrane base plate 45cm x 45cm for TC5



Overview

The membrane-based panels from Secabo open up many new opportunities to use a Secabo heat press - especially in transfer objects with large height differences and uneven spots. Many old and almost all new transfer presses models are suitable for retrofitting with passive membrane-bottom plates. A small fan Ball, the membrane can be easily inflated. Thus, the maximum compensation amount of the membrane can be determined for a transfer. The contact pressure is adjusted as usual at the transfer press, for example a wheel on the hot plate. A pressure gauge shows the closed state of the transfer press the current pressure to reliably - in grams per square centimeter. During the pressing process, the pressure by the blower ball and a drain valve can be finely adjusted. With the membrane-bottom plates of Secabo can be read not only the actual transfer printing, but also reproducibly adjusted repeatedly. The membrane-bottom plates for work surfaces of 38cm x 38cm and 40cm x 50cm. The membrane plates have even dimensions of 45cm x45cm x 57cm or 47cm. They can be mounted directly on the base of many Secabo heat presses and are also known for the quick-change systems and Slide extensions from Secabo.



membrane base plate 45cm x 45cm for TC5

technical data

working area 38cm x 38cm

Setting on the transfer press, fine adjustment on fan and ball

drain valve

max. working pressure depending on the performance of the transfer press to 500

g/cm²

max temperature 230 °C

pressure setting

environment $5 \circ C - + 35 \circ C / 30\% - 70\%$ humidity

dimensions 45cm x 45cm x 5.5cm

net weight 10 kg

scope of delivery

Membrane-bottom plate with Anschraubsockel, fastening

material



membrane base plate 45cm x 45cm for TC5

views

